




HygroMATIK[®]
WE HUMIDIFY THE AIR

HygroMatik DDS

The new generation
of steam injection humidifiers



HygroMATIK
MORE THAN
45 YEARS
HUMIDIFICATION



Humidification for best conditions

for industry, manufacturing processes, public buildings and offices.

The new generation

The new HygroMatik DDS, the only system offering four components in one compact unit. High performance separator, strainer, condensate drain and start-up safety feature – all in high grade stainless steel, compact, light and energy efficient.

The DDS can be configured individually. The standard flanged connections, compact dimensions and light weight ensure easy installation – even where available space is at a premium.

The HygroMatik DDS humidifies with condensate-free saturated steam and offers the shortest absorption distances.



The new DDS. Go green!

- The only 4 in 1 system
- Most compact dimensions and least weight
- Best energy efficiency
- Easy installation
- Flexible modular construction
- Customer-specific solutions

Exchangeable strainer

The high-quality stainless steel strainer protects the actuator and the condensate drain from foreign particles from the steam network.


The internal fine-mesh strainer can be exchanged when necessary.

High performance separator

The stainless steel separator separates steam from condensate using a spiral shaped guidance system. The low weight and compact closed-system makes the HygroMatik DDS easy to install and energy efficient.

Reliable start-up safety feature

The start-up safety feature switches on humidification only after a specified temperature has been reached. This effectively prevents condensate carryover from the steam network into the air conditioning ducting.



Flexible


All DDS components are light, simple to install and can be individually configured. It will fit anywhere.



Optimum regulation

The bus compatible actuator ensures optimum control. The special metal-to-metal or soft sealing HygroMatik actuator-valve controls the steam flow via valve-lift with percentual characteristic curve. This means:


- Especially fine control in lower ranges
- Rapid reaction for high humidification requirements in higher ranges



Stainless steel steam lances

They have low weight and are easily installed. Low-noise steam nozzles take steam from the driest areas of the steam lance.

The nozzles are positioned against the air-flow direction which ensures fast distribution and short absorption distances.



The internal, closed-system steam lance heating system

It is located at the lowest point on the steam lances so that any possible condensate can be vaporized immediately. The light and maintenance-friendly thermal condensate drain discharges condensate out of the heating system. The heating system is supplied directly from the separator or, alternatively, from a separate steam supply.


- Space-saving through internal heating system
- Rapid regulation during start-up through pre-heated steam lances
- No air-flow heating

High performance condensate drain


The robust, tight-sealing, ball-float condensate drain discharges condensate. Due to the fast-reaction operating principle and high capacity it can handle large amounts of condensate which are discharged away, for instance when starting the system. The closed-system approach prevents steam loss.

Our service for you

- Technical hotline: +49 4193 895-293 or hotline@hygromatik.com
- Manuals and information material at www.hygromatik.com



DDS installation schematic



HYGROMATIK
WE HUMIDIFY THE AIR

Source of cover pictures:
Lilly Forschung GmbH, Hamburg, Germany

HygroMatik GmbH
Lise-Meitner-Str. 3
24558 Henstedt-Ulzburg
Germany
T +49 4193 895-231
F +49 4193 895-33
axel.zadina@hygromatik.de
www.hygromatik.com

HygroMatik USA
PO Box 10084
Lancaster, PA 17605
USA
T 717 299 5679
F 717 299 5679
info@hygromatikusa.com
www.hygromatik.com

A Member of the **spirax**/**sarco** group

